

Part #	Product #	Pitch (in.)	Profile	Width (in.)	Roll Length (ft.)
XL-025-200-LLUK	77870157	0.2	Timing	0.25	200
XL-050-100-LLUSNT	77870020	0.2	Timing	0.5	100
XL-037-100-LLUSNT	77870018	0.2	Timing	0.38	100
XL-037-200-LLUSNT	77870017	0.2	Timing	0.38	200
XL-025-100-LLUSNT	77870014	0.2	Timing	0.25	100
XL-025-200-LLUSNT	77870013	0.2	Timing	0.25	200
XL-050-100-LLUS	77870008	0.2	Timing	0.5	100
XL-050-200-LLUS	77870007	0.2	Timing	0.5	200
XL-037-100-LLUS	77870006	0.2	Timing	0.38	100
XL-037-200-LLUS	77870005	0.2	Timing	0.38	200
XL-031-100-LLUS	77870004	0.2	Timing	0.31	100
XL-031-200-LLUS	77870003	0.2	Timing	0.31	200
XL-025-100-LLUS	77870002	0.2	Timing	0.25	100
XL-025-200-LLUS	77870001	0.2	Timing	0.25	200
L-100-100-LLUKNT	77870497	0.375	Timing	1	100
L-075-100-LLUK	77870480	0.375	Timing	0.75	100
L-150-100-LLUSNT	77870344	0.375	Timing	1.5	100
L-150-200-LLUSNT	77870343	0.375	Timing	1.5	200
L-100-100-LLUSNT	77870342	0.375	Timing	1	100
L-100-200-LLUSNT	77870341	0.375	Timing	1	200
L-075-100-LLUSNT	77870340	0.375	Timing	0.75	100
L-075-200-LLUSNT	77870339	0.375	Timing	0.75	200
L-050-100-LLUSNT	77870338	0.375	Timing	0.5	100
L-050-200-LLUSNT	77870337	0.375	Timing	0.5	200
L-037-100-LLUSNT	77870336	0.375	Timing	0.38	100
L-150-100-LLUS	77870329	0.375	Timing	1.5	100
L-150-200-LLUS	77870328	0.375	Timing	1.5	200
L-100-100-LLUS	77870327	0.375	Timing	1	100
L-100-200-LLUS	77870326	0.375	Timing	1	200
L-075-100-LLUS	77870325	0.375	Timing	0.75	100
L-075-200-LLUS	77870324	0.375	Timing	0.75	200
L-050-100-LLUS	77870323	0.375	Timing	0.5	100
L-050-200-LLUS	77870322	0.375	Timing	0.5	200
L-037-100-LLUS	77870321	0.375	Timing	0.38	100
L-037-200-LLUS	77870320	0.375	Timing	0.38	200
H-400-200-LLUSHFNT	77871004	0.5	Timing	4	
H-100-100-LLUKNT	77870835	0.5	Timing	1	100
H-075-100-LLUKNT	77870833	0.5	Timing	0.75	100
H-050-100-LLUKNT	77870831	0.5	Timing	0.5	100
H-300-200-LLUK	77870822	0.5	Timing	3	200
H-200-100-LLUK	77870821	0.5	Timing	2	100

Part #	Product #	Pitch (in.)	Profile	Width (in.)	Roll Length (ft.)
H-150-100-LLUK	77870819	0.5	Timing	1.5	100
H-100-100-LLUK	77870817	0.5	Timing	1	100
H-075-100-LLUK	77870814	0.5	Timing	0.75	100
H-050-100-LLUK	77870812	0.5	Timing	0.5	100
H-200-100-LLUSNT	77870665	0.5	Timing	2	100
H-150-100-LLUSNT	77870663	0.5	Timing	1.5	100
H-100-100-LLUSNT	77870660	0.5	Timing	1	100
H-075-100-LLUSNT	77870658	0.5	Timing	0.75	100
H-050-100-LLUSNT	77870656	0.5	Timing	0.5	100
H-400-100-LLUS	77870649	0.5	Timing	4	100
H-300-100-LLUS	77870646	0.5	Timing	3	100
H-200-100-LLUS	77870644	0.5	Timing	2	100
H-200-200-LLUS	77870643	0.5	Timing	2	200
H-150-100-LLUS	77870642	0.5	Timing	1.5	100
H-100-100-LLUS	77870640	0.5	Timing	1	100
H-100-200-LLUS	77870639	0.5	Timing	1	200
H-075-100-LLUS	77870638	0.5	Timing	0.75	100
H-075-200-LLUS	77870637	0.5	Timing	0.75	200
H-050-100-LLUS	77870636	0.5	Timing	0.5	100
H-050-200-LLUS	77870635	0.5	Timing	0.5	200
XH-200-100-LLUS	77871065	0.875	Timing	2	100
XH-150-100-LLUS	77871063	0.875	Timing	1.5	100