



DRIVEN BY POSSIBILITY™

GATES FLEX SERIES

HYDRAULIC CRIMPING EQUIPMENT

GC32FLEX TSI | GC32FLEX HEAD ONLY UNIT | GC32FLEX HYDRAULIC POWER UNIT

A CRIMPER MADE TO FLEX

Gates Flex Series hydraulic crimping equipment takes assembly fabrication to the next level by providing flexibility, connectivity, precision, intelligence, efficiency and value at the push of a button. Designed for low volume shop production, this crimper makes 2" assemblies accessible for small to medium sized operations. The digital tablet command interface with continuously updated eCrimp™ specifications enables precise, efficient and error-free crimping. Even in remote environments, this crimper flexes its portability via built-in forklift slots and user-supplied pump capability. Its modular design allows users to level up crimp operations in its product offering of a hydraulic crimper head only unit, hydraulic power unit, or fully integrated GC32FLEX TSI 2" crimper. The highly engineered capabilities are backed by Gates world-class team of engineering support and result in an industry-leading solution that can drive endless possibilities for customers.

HIGHLIGHTS + SPECIFICATIONS

GC32FLEX TSI & GC32FLEX HEAD ONLY UNIT

- Crimp up to 2" 6-wire spiral hose
- Smart technology tablet command interface
- Access for large elbows and long drops
- Quick change die sets installed without press operation
- Color coded dies
- Horizontal feed
- 2.5" return line
- Head only unit is compatible with any 10,000 PSI power unit
- 18"H x 29"W x 25"D
- Crimper stand and die rack available

GC32FLEX HYDRAULIC POWER UNIT

- Integrated 2-stage power unit is fully compatible with and increases crimp speed of GC32FLEX head-only unit
- Precision contactless digital sensor
- Includes hands-free foot pedal
- Includes die change tool
- Includes integrated tablet charging command

FLEX YOUR CRIMP OPERATIONS

GATES FLEX SERIES

Enhance your capabilities for hydraulic assembly fabrication with the latest in crimper technology.

FLEXIBLE

- Modular design provides different points of entry for crimper upgrades
- Safe and easy transport via forklift slots
- No WiFi needed for operation, only for updates & remote support
- GC32FLEX head only unit can be run on any 10,000PSI 2L hydraulic power pack for assembly in remote areas

CONNECTED

- Command interface with wireless connectivity and eCrimp control
- Access to continuously updated eCrimp product specs
- Remote support available via the command interface to quickly troubleshoot
- Wireless software updates

PRECISE

- Sensor accuracy
- Bluetooth measurement calipers for wireless measurement verification

INTELLIGENT

- Learning algorithm produces repeatable results
- Learns from user input so there is no need to calibrate the sensors
- Maintains history of all completed crimps

EFFICIENT

- Horizontal feed with rear and front-loading ability
- Easy to calibrate
- Color coded dies
- Crimp using on-screen button or foot pedal

ECONOMICAL

- Fit-for-purpose crimper made for low volume 2" assembly production



GC32FLEX TSI HYDRAULIC CRIMPER
Part No: 78395 / Product No: 7480-0013
(Pictured with stand and die rack sold separately.)



GC32FLEX HYDRAULIC CRIMPER (HEAD ONLY)
Part No: 78818 / Product No: 7480-7009



GC32FLEX HYDRAULIC POWER UNIT
Part No: 78087 / Product No: 7482-0123



Gates exclusive database containing the most up-to-date specifications for Gates hydraulic and industrial hose products including crimping instructions, crimp diameter and maintenance/troubleshooting information. GC32FLEX embeds eCrimp with continuous updates via WiFi for the most current product and crimp data available.