

CenterClean Sprocket Specifications

	CC40								
Number of Teeth		10	11	12	13	15	16	17	20
Nom. Outside Diameter	inch	4.9	5.4	5.9	6.4	7.4	7.9	8.4	9.9
	mm	124	137	150	163	188	201	213	251
Nominal Width	inch	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
	mm	165	165	165	165	165	165	165	165
Imperial Square Bore - Dimension	inch	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
Material	UHMW-PE								



Notes: CC40 belts run on most 40 mm pitch sprockets.

Sprockets must be locked into position on the shaft.