

Fabrication

V-GUIDES

V-Guide Specifications

Metric	Size	W1	W2*	Height	Durometer (Shore A)	Min. Pulley Dia.	Color
	Nearest English						
K6	000	0.236" (6 mm)	0.157" (4 mm)	0.157" (4 mm)	78	2.0"	PosiBlue
K8	Z	0.313" (8 mm)	0.157" (4 mm)	0.197" (5 mm)	78	2.0"	PosiBlue
K10	O	0.394" (10 mm)	0.236" (6 mm)	0.236" (6 mm)	78	2.5"	PosiBlue
	A Modified	0.472" (12 mm)	0.354" (9 mm)	0.217" (5.5 mm)	78	3.0"	PosiBlue
K13	A	0.512" (13 mm)	0.276" (7 mm)	0.315" (8 mm)	78	3.0"	PosiBlue
K17	B	0.669" (17 mm)	0.394" (10 mm)	0.433" (11 mm)	78	4.5"	PosiBlue
V-Guide Length Capabilities							
Minimum Belt Length		80" (2.0 m)					
Maximum Belt Length		140' (42.7 m)					

* For reference only

