

Part #	Product #	Pitch (mm)	Profile	Width (mm)	Roll Length (m)
AT5-25-50M-LLUK	77874192	5	Metric AT	25	50
AT5-20-50M-LLUK	77874190	5	Metric AT	20	50
AT5-15-50M-LLUK	77874188	5	Metric AT	15	50
AT5-10-50M-LLUK	77874186	5	Metric AT	10	50
AT5-50-30M-LLUSNT	77874038	5	Metric AT	50	30
AT5-50-50M-LLUS	77874021	5	Metric AT	50	50
AT5-32-50M-LLUS	77874019	5	Metric AT	32	50
AT5-25-50M-LLUS	77874017	5	Metric AT	25	50
AT5-20-50M-LLUS	77874015	5	Metric AT	20	50
AT5-15-50M-LLUS	77874013	5	Metric AT	15	50
AT5-10-50M-LLUS	77874011	5	Metric AT	10	50
T5-75-30M-LLUKNT	77873205	5	Metric T	75	30
T5-75-60M-LLUKNT	77873204	5	Metric T	75	60
T5-100-50M-LLUK	77873190	5	Metric T	100	50
T5-75-50M-LLUK	77873188	5	Metric T	75	50
T5-50-50M-LLUK	77873186	5	Metric T	50	50
T5-50-100M-LLUK	77873185	5	Metric T	50	100
T5-32-50M-LLUK	77873184	5	Metric T	32	50
T5-32-100M-LLUK	77873183	5	Metric T	32	100
T5-25-50M-LLUK	77873182	5	Metric T	25	50
T5-25-100M-LLUK	77873181	5	Metric T	25	100
T5-20-50M-LLUK	77873180	5	Metric T	20	50
T5-20-100M-LLUK	77873179	5	Metric T	20	100
T5-15-50M-LLUK	77873178	5	Metric T	15	50
T5-15-100M-LLUK	77873177	5	Metric T	15	100
T5-10-50M-LLUK	77873176	5	Metric T	10	50
T5-10-100M-LLUK	77873175	5	Metric T	10	100
T5-32-50M-LLUSHB	77873096	5	Metric T	32	
T5-50-30M-LLUSNT	77873029	5	Metric T	50	30
T5-32-30M-LLUSNT	77873027	5	Metric T	32	30
T5-25-30M-LLUSNT	77873025	5	Metric T	25	30
T5-25-60M-LLUSNT	77873024	5	Metric T	25	60
T5-20-30M-LLUSNT	77873023	5	Metric T	20	30
T5-15-30M-LLUSNT	77873021	5	Metric T	15	30
T5-15-60M-LLUSNT	77873020	5	Metric T	15	60
T5-10-30M-LLUSNT	77873019	5	Metric T	10	30
T5-10-60M-LLUSNT	77873018	5	Metric T	10	60
T5-20-50M-LLUS	77873016	5	Metric T	20	50
T5-100-50M-LLUS	77873015	5	Metric T	100	50
T5-75-50M-LLUS	77873013	5	Metric T	75	50
T5-50-50M-LLUS	77873011	5	Metric T	50	50

Part #	Product #	Pitch (mm)	Profile	Width (mm)	Roll Length (m)
T5-50-100M-LLUS	77873010	5	Metric T	50	100
T5-32-50M-LLUS	77873009	5	Metric T	32	50
T5-32-100M-LLUS	77873008	5	Metric T	32	100
T5-25-50M-LLUS	77873007	5	Metric T	25	50
T5-25-100M-LLUS	77873006	5	Metric T	25	100
T5-20-100M-LLUS	77873004	5	Metric T	20	100
T5-15-50M-LLUS	77873003	5	Metric T	15	50
T5-15-100M-LLUS	77873002	5	Metric T	15	100
T5-10-50M-LLUS	77873001	5	Metric T	10	50
T5-10-100M-LLUS	77873000	5	Metric T	10	100
5HTD-25-50M-LLUK	77872055	5	HTD	25	50
5HTD-15-50M-LLUK	77872053	5	HTD	15	50
5HTD-10-50M-LLUK	77872051	5	HTD	10	50
5HTD-50-50M-LLUS	77872007	5	HTD	50	50
5HTD-25-50M-LLUS	77872005	5	HTD	25	50
5HTD-15-50M-LLUS	77872003	5	HTD	15	50
5HTD-15-100M-LLUS	77872002	5	HTD	15	100
5HTD-10-50M-LLUS	77872001	5	HTD	10	50
8HTD-32-50M-LLUS	77872109	8	HTD	32	50
8HTD-25-50M-LLUS	77872107	8	HTD	25	50
8HTD-20-50M-LLUS	77872105	8	HTD	20	50
8HTD-20-100M-LLUS	77872104	8	HTD	20	100
8HTD-15-50M-LLUS	77872103	8	HTD	15	50
8HTD-10-50M-LLUS	77872101	8	HTD	10	50
AT10-50-30M-LLUSNT	77874386	10	Metric AT	50	30
AT10-40-30M-LLUSNT	77874384	10	Metric AT	40	30
AT10-32-30M-LLUSNT	77874382	10	Metric AT	32	30
AT10-25-30M-LLUSNT	77874380	10	Metric AT	25	30
AT10-20-30M-LLUSNT	77874378	10	Metric AT	20	30
AT10-75-50M-LLUS	77874371	10	Metric AT	75	50
AT10-50-50M-LLUS	77874369	10	Metric AT	50	50
AT10-40-50M-LLUS	77874367	10	Metric AT	40	50
AT10-32-50M-LLUS	77874365	10	Metric AT	32	50
AT10-25-50M-LLUS	77874363	10	Metric AT	25	50
AT10-25-100M-LLUS	77874362	10	Metric AT	25	100
AT10-20-50M-LLUS	77874361	10	Metric AT	20	50
T10-25-60M-LLUKNTB	77873557	10	Metric T	25	60
T10-50-50M-LLUK	77873517	10	Metric T	50	50
T10-32-50M-LLUK	77873515	10	Metric T	32	50
T10-25-50M-LLUK	77873513	10	Metric T	25	50
T10-32-60M-LLUSNB	77873384	10	Metric T	32	60

Part #	Product #	Pitch (mm)	Profile	Width (mm)	Roll Length (m)
T10-100-30M-LLUSNT	77873376	10	Metric T	100	30
T10-75-30M-LLUSNT	77873374	10	Metric T	75	30
T10-50-30M-LLUSNT	77873372	10	Metric T	50	30
T10-32-30M-LLUSNT	77873370	10	Metric T	32	30
T10-25-30M-LLUSNT	77873368	10	Metric T	25	30
T10-25-60M-LLUSNT	77873367	10	Metric T	25	60
T10-20-30M-LLUSNT	77873366	10	Metric T	20	30
T10-100-50M-LLUS	77873361	10	Metric T	100	50
T10-75-50M-LLUS	77873359	10	Metric T	75	50
T10-50-50M-LLUS	77873357	10	Metric T	50	50
T10-50-100M-LLUS	77873356	10	Metric T	50	100
T10-32-50M-LLUS	77873355	10	Metric T	32	50
T10-32-100M-LLUS	77873354	10	Metric T	32	100
T10-25-50M-LLUS	77873353	10	Metric T	25	50
T10-25-100M-LLUS	77873352	10	Metric T	25	100
T10-20-50M-LLUS	77873351	10	Metric T	20	50
AT20-100-50M-LLUKNTB	77874891	20	Metric AT	100	50
AT20-25-50M-LLUK	77874843	20	Metric AT	25	50
AT20-100-50M-LLUSNTB	77874758	20	Metric AT	100	50
AT20-100-25M-LLUS	77874719	20	Metric AT	100	25
T20-50-50M-LLUK	77873874	20	Metric T	50	50