



TPU BELTS


THERMOPLASTIC POLYURETHANE

REPLACEMENT FOOD GRADE FORM


*Name:	*Phone:	*Email:
*Company Name:	*Site Location:	
*Briefly describe what is being replaced:		
Fill out one of the three lines below		
*Max. Load:	lbs.	
*Load Rate:	lbs/hr	and Conveyor Speed: ft/min
*Lb per cubic foot:		and Depth of Product: in

Belt Pitch:
Belt Width:
Belt Length:
Splice Type
Mechanical:
Weld:
Straight Cleats (5mm thick)
Height:
Spacing:
Scoop Cleats (7mm thick)
Height:
Spacing:
Sidewalls:
Height:
Offset of Cleat/Sidewall (in/mm):
Application Wet or Dry?:


Common Pitch Types




PC10



PC20




CC40




FC12

*Measurements are between sprockets, center to center

STRAIGHT CONVEYOR



Z-CONVEYOR



*Sprocket information only needed if changing pitch

ADDITIONAL OPTIONAL INFORMATION	Comments:
*Number of sprockets:	
Diameter of sprocket:	
Or number of teeth:	
Carryway material:	
Slider bed or Wear strips?	
Material:	

GATES TPU
 9 Northwestern Drive Salem, NH 03079, U.S.A.
 Tel. +1 (603) 890-1515. / +1 (800) 394-4844.
contact@gates.com
www.gates.com/TPU

Application Engineering
[email: slo.apps@gates.com](mailto:slo.apps@gates.com)
 Tel. +1 (800) 505-8494