



TPU BELTS

THERMOPLASTIC POLYURETHANE

GATES TPU FOOD BELT QUOTE CHECKLIST STRAIGHT CONVEYOR

*Name: *Phone: *Email: *Company Name: *Site Location:

APPLICATION

*Briefly describe what is being conveyed, what type of belt is being replaced.

*Max. Load lbs.

*Load Rate lbs/hr and Conveyor Speed ft/min

*Lb per Cubic Ft. and Depth of Product in

BELT

INPUT

*Belt Pitch/Type

*Belt Width (in/mm)

*Belt Length (in/mm)

*Splice Type

Mechanical

Weld

*Straight Cleats (5mm thick)

Overall Height

Spacing

Offset From Edge (in/mm) / Centered

*Scoop Cleats (7 mm thick)

Overall Height

Spacing

Offset From Edge (in/mm) / Centered

*Sidewalls

Overall Height

Offset From Edge (in/mm)

V-Guide

Type

Offset From Edge (in/mm) / Centered

SPROCKETS

of Sprockets

Number of Teeth or Diameter

Bore Type

Dimension (in/mm)

Keyway Dimension (in/mm)

Any Back Idlers

Diameter of Back Bend (in/mm)

Smallest In Conveyor (in/mm)

Drum Motor / Motorized Pulley

CONVEYOR

Bed Type

Wear Strips

Number Across Conveyor Width

Spacing

Pattern

*Material

or Slider Bed

Dimensions (in/mm)

*Material

Roller

Number of Rollers

Spacing of Rollers

Returnway

Conveyor Sidewalls/Fenders - Height

Material

Troughing

Transition Length (in/mm)

Angle

Side Wear Strips

Drive Type

Incline Angle

Angle of Belt Wrap On Drive Pulley

Tensioning Device (Take Up) Avail


Type

Total Travel

Extended Distance When Center Distance


Is Measured

*




Comments (environment, cleaning protocol, etc.)


Common Pitch Types




PC10



PC20



CC40



FC12

ADDITIONAL INFORMATION

*Dry/Wet Application

Outside Sales Contact Info

GATES TPU

9 Northwestern Drive Salem, NH 03079, U.S.A.
Tel. +1 (603) 890-1515. / +1 (800) 394-4844.
contact@gates.com
www.gates.com/TPU

Application Engineering
email: slo.apps@gates.com
Tel. +1 (800) 505-8494